

Position indicator SASF-S3-B-F-A30

Part number: 8140397

FESTO



Data sheet

 [General operating condition](#)

Feature	Value
Adjustment range of swivel angle	0 deg ... 180 deg
Connection point for positioner and position sensor conforms to standard	VDI/VDE 3845 Size AA 2
Dimensions W x L x H	Ø 40 x 43
Vibration resistance	Transport application test with severity level 2 as per FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 as per FN 942017-5 and EN 60068-2-27
LABS (PWIS) conformity	VDMA24364 Zone III
Ambient temperature	-25 °C ... 70 °C
Product weight	26 g
Type of mounting	As per VDI/VDE 3845
Housing colour	Black
Note on materials	RoHS compliant
Spacer element material	PP
Housing material	PP high-alloy stainless steel
Material of screws	high-alloy stainless steel