


Double nipple NPFC-DS-M5-G18-M

Part number: 8142591

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Threaded fitting material | Brass, nickel-plated |
| Pack size | 10 |
| Operating pressure | -0.95 bar ... 10 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [:-:-] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Nominal tightening torque, pneumatic connection 1 | 10.55 Nm |
| Nominal tightening torque, pneumatic connection 2 | 1.78 Nm |
| Tolerance for nominal tightening torque | ± 20% |
| Product weight | 8.96 g |
| Pneumatic connection 1 | G1/8 |
| Pneumatic connection 2 | M5 |
| Note on materials | RoHS-compliant |
| Seals material | PVC |