

Reducing nipple NPFC-RS-G1-G34-MF

Part number: 8142602

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Threaded fitting material	Brass, nickel-plated
Pack size	10
Operating pressure	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [-:~:]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C ... 60 °C
Nominal tightening torque, pneumatic connection 1	62.5 Nm
Tolerance for nominal tightening torque	±20%
Product weight	97.09 g
Pneumatic connection 1	G1
Pneumatic connection 2	G3/4
Note on materials	RoHS compliant
Seals material	PVC