

Cable fitting NETC-M20-PBU-T26-EX4-E

Part number: 8151587

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|---|
| Ambient temperature | -40 °C ... 75 °C |
| Degree of protection | IP66 IP68 |
| Note on degree of protection | IP68 at 5 bar for 30 minutes |
| ATEX category gas | II 2G |
| ATEX category for dust | II 2D |
| Type of ignition protection for gas | Ex eb IIC Gb |
| Type of (ignition) protection for dust | Ex tb IIIC Db |
| Explosive ambient temperature | -40°C ≤ Ta ≤ +75°C |
| Explosion protection certification outside the EU | EPL Db (IEC-EX) EPL Gb (IEC-EX) |
| CE marking (see declaration of conformity) | as per EU explosion protection directive (ATEX) As per EU RoHS directive |
| Size | M20x1.5 |
| Cable diameter | 7 mm ... 13 mm |
| Color | Blue/black |
| Material for cable connector | PA |
| Seals material | EPDM |
| Product weight | 13 g |
| Pack size | 1 |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Note on materials | RoHS-compliant |