

Cable fitting NETC-M20-PBK-T14

Part number: 8151590

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Ambient temperature	-40 °C ... 100 °C
Degree of protection	IP66 IP68
Note on degree of protection	IP68 at 5 bar for 30 minutes
CE marking (see declaration of conformity)	As per EU RoHS directive
Size	M20x1.5
Cable diameter	4 mm ... 13 mm
Color	Black
Material for cable connector	PA
Seals material	EPDM
Product weight	14 g
Pack size	1
LABS (PWIS) conformity	VDMA24364 Zone III
Note on materials	RoHS compliant