

Connection kit DADG-AK-G8-12-100

Part number: 8152379

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|---|
| Size | 12 |
| Stroke | 100 mm |
| Operating pressure | 0.1 MPa ... 0.8 MPa |
| Operating pressure | 1 bar ... 8 bar |
| Operating pressure | 14.5 psi ... 116 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Max. tightening torque | 1.5 Nm |
| Tightening torque tolerance | ±10% |
| Max. tightening torque, pneumatic connection 1 | 0.7 Nm |
| Product weight | 19.2 g |
| Pneumatic connection | M5 |
| Adapter material | Epoxy |
| Seals material | NBR |
| Material of screws | Coated steel |