

Connection kit DADG-AK-G8-16-80

Part number: 8152385

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	16
Stroke	80 mm
Operating pressure	0.1 MPa ... 0.8 MPa
Operating pressure	1 bar ... 8 bar
Operating pressure	14.5 psi ... 116 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque	1.5 Nm
Tightening torque tolerance	±10%
Max. tightening torque, pneumatic connection 1	0.7 Nm
Product weight	17.8 g
Pneumatic connection	M5
Adapter material	Epoxy
Seals material	NBR
Material of screws	Coated steel