

# Sealing ring OL-1

Part number: 8153156

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Based on norm	ISO 16030
Operating pressure for entire temperature range	-0.095 MPa ... 3 MPa
Operating pressure for entire temperature range	-0.95 bar ... 30 bar
Operating pressure for entire temperature range	-13.775 psi ... 435 psi
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 100 °C
Manual tightening at RT	Yes
Nominal tightening torque	23 Nm
Tolerance for nominal tightening torque	±20%
Product weight	1.09 g
Pneumatic connection	G1
Note on materials	RoHS compliant
Stops material	Aluminum
Seals material	HNBR