


Operator unit CDPX-X-E2-W-15-EX2

Part number: 8155222

FESTO



 General operating condition

Data sheet

Feature	Value
Width	399 mm
Installation depth	17 mm
Height	248 mm
Length	43 mm
Max. front panel thickness	26 mm
Real-time clock	Yes
Supported PLC protocols	CODESYS 3.X ModbusRTU Client Modbus RTU server Modbus TCP Client Modbus TCP server
Real-time clock deviation	<100 ppm at 25°C
Number of colors	16 M
Display	With backlighting
Display type	Color TFT
Display properties	Touchscreen
Display size	15.6"
Backup battery	Rechargeable lithium battery
Display resolution	1366x768 pixels
Electrical power consumption	23 W
Certification	c UL us - Listed (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364 Zone III
Storage temperature	-30 °C ... 80 °C
Relative air humidity	5 - 85% Non-condensating
Degree of protection	IP67
Note on degree of protection	In mounted state
Ambient temperature	-20 °C ... 55 °C
Note on ambient temperature	for vertical mounting
Product weight	4000 g
Type of mounting	VESA interface
Note on materials	RoHS compliant
Ethernet interface, connection type	Socket
Ethernet interface, connection technology	RJ45

Feature	Value
Ethernet interface, number of poles/wires	8
Ethernet interface, transmission rate	10/100 mbps
Ethernet interface, function	Programming Power supply PoE
Ethernet interface, specification	IEEE 802.3 af/at
USB interface, function	File transfer
USB-interface, connection type	Socket
USB interface	USB 2.0, type A
Programming software	Designer Studio
CPU data	2 GB RAM
Explosion protection certification outside the EU	Class I, Div. 2 (US)
Explosion prevention and protection	Class I, Div. 2 (US)
Certificate issuing authority	UL E239998 UL E245518