


Axial kit EAMM-A-K62-150A

Part number: 8157271

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Transferable torque	47 Nm
Product weight	1672 g
Interface code, actuator	K62
Interface code, motor in	140A 150A
Note on materials	RoHS compliant