

Push-in Y-connector NPQE-Y-Q4-E-F1A-P10

Part number: 8158804

FESTO



 General operating condition

Data sheet

| Feature | Value |
|---|--|
| Size | Mini |
| Nominal width | 2.3 mm |
| Mounting position | Any |
| Design | Y-shape |
| Pack size | 10 |
| Structural design | Push-pull principle |
| Variants | Metals with copper, zinc or nickel by mass as main constituent are excluded from use. Exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils. |
| Operating pressure for entire temperature range | -0.095 MPa ... 0.8 MPa |
| Operating pressure for entire temperature range | -0.95 bar ... 8 bar |
| Operating pressure for entire temperature range | -13.775 psi ... 116 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Suitability for the production of Li-ion batteries | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 4 according to ISO 14644-1 |
| Ambient temperature | -5 °C ... 60 °C |
| Product weight | 2.1 g |
| Pneumatic connection 1 | for pneumatic tubing outside diameter 4 mm |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 4 mm |
| Releasing ring color | Blue |
| Note on materials | RoHS-compliant |
| Housing material | PBT |
| Releasing ring material | POM |
| Material of tubing seal | NBR |
| Material of tube retaining claw | High-alloy stainless steel |