

Disposable tip DHAP-20-TA1-P960S

Part number: 8160282

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Volume	0.02 cm ³
Pack size	960
Structural design	Pipette tip holder for 20...1000 µl single-use tips from Festo
Packing type	Stack
Bioburden	ATP: < 2·10 ⁻¹² mg/µl BSE / TSE: free DNA: <32 pg human DNA DNase: ≤ 5·10 ⁻⁷ Kunitz units/µl Endotoxin: ≤ 0.001 EU/ml RNase: ≤ 5·10 ⁻⁹ Kunitz units/µl
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	5 °C ... 40 °C
Note on storage temperature	short-term for transport in packaging -25 ... 55 °C
Relative air humidity	10 - 90% Non-condensing
Ambient conditions	Atmospheric pressure 80 ... 106 kPa
Ambient temperature	5 °C ... 40 °C
Note on materials	RoHS-compliant
Pipette tip material	PP