

# Shock absorber DYSD-Q11-16-15-Y1F-Y9

Part number: 8161528

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	16
Stroke	15 mm
Cushioning	Self-adjusting
Mounting position	Any
Position sensing	None
Symbol	00991495
Max. impact velocity	1 m/s
Reset time at room temperature	0.3 s
Mode of operation	Pushing Single-acting
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Cushioning length	15 mm
Max. stop force	2000 N
Max. energy absorption per stroke	40 J
Max. energy absorption per hour	64000 J
Max. residual energy	0.16 J
Resetting force	46 N
Min. insertion force	160 N
Product weight	220 g
Type of mounting	With lock nut
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Steel, galvanized
Piston rod material	High-alloy steel
Nut material	Steel, galvanized