


# Shock absorber DYSD-Q11-20-16-Y1F-Y9

Part number: 8161530

FESTO



 General operating condition

## Data sheet

Feature	Value
Size	20
Stroke	16 mm
Cushioning	Self-adjusting
Mounting position	Any
Position sensing	None
Symbol	00991495
Max. impact velocity	1 m/s
Reset time at room temperature	0.3 s
Mode of operation	Pushing Single-acting
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C ... 60 °C
Cushioning length	16 mm
Max. stop force	3000 N
Max. energy absorption per stroke	70 J
Max. energy absorption per hour	92000 J
Max. residual energy	0.32 J
Resetting force	75 N
Min. insertion force	260 N
Product weight	385 g
Type of mounting	With lock nut
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Steel, galvanized
Piston rod material	High-alloy steel
Nut material	Steel, galvanized