

# Guided drive DFM-25-200-B-PPV-A-GF

Part number: 8165513

FESTO



 General operating condition

## Data sheet

| Feature   | Value  |
|---|--|
| Stroke  | 200 mm   |
| Piston diameter   | 25 mm  |
| Drive unit operating mode                                 | Yoke   |
| Cushioning  | Pneumatic cushioning, adjustable at both ends                      |
| Mounting position   | Any  |
| Guide   | Sliding guide  |
| Structural design   | Guide  |
| Position sensing  | For proximity sensor   |
| Operating pressure  | 0.15 MPa ... 1 MPa   |
| Operating pressure  | 1.5 bar ... 10 bar   |
| Mode of operation   | Double-acting  |
| Operating medium  | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media                  | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)                          | 2 - Moderate corrosion stress                                      |
| LABS (PWIS) conformity                                    | VDMA24364-B1/B2-L  |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 6 according to ISO 14644-1                                   |
| Ambient temperature                                       | -20 °C ... 80 °C   |
| Impact energy in the end positions                        | 0.3 J  |
| Theoretical force at 6 bar, retracting                    | 247 N  |
| Theoretical force at 6 bar, advancing                     | 295 N  |
| Alternative connections                                   | See product drawing  |
| Pneumatic connection                                      | G1/8   |
| Note on materials   | RoHS-compliant   |
| Cover material  | Wrought aluminum alloy   |
| Seals material  | NBR  |
| Housing material  | Wrought aluminum alloy   |
| Piston rod material                                       | High-alloy stainless steel   |