

Sensor mounting DASP-V4-12-A-R1

Part number: 8174844

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	12
Design	for tie rods
Mounting position	Any
for piston Ø	Ø80 Ø100 Ø125
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 120 °C
Tightening torque	0.6 Nm ... 1 Nm
Product weight	39 g
Type of mounting	Clamped
Note on materials	RoHS-compliant
Retainer bracket material	High-alloy stainless steel
Material of screws	High-alloy stainless steel