

Sensor mounting DASP-V4-12-A-R1

Part number: 8174844

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|--|
| Size | 12 |
| Design | For tie rods |
| Mounting position | Any |
| for piston Ø | Ø80 Ø100 Ø125 |
| Corrosion resistance class (CRC) | 4 - Particularly high corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C ... 120 °C |
| Tightening torque | 0.6 Nm ... 1 Nm |
| Product weight | 39 g |
| Type of mounting | Clamped |
| Note on materials | RoHS compliant |
| Retainer bracket material | high-alloy stainless steel |
| Material of screws | high-alloy stainless steel |