


Hand lever valve H-5-1/4-B

Part number: 8995

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|----------------------|
| Valve function | 5/2-way, bistable |
| Normal nominal flow rate (normalized to DIN 1343) | 550 l/min |
| Pneumatic working port | G1/4 |
| Operating pressure | -0.95 bar ... 10 bar |
| Structural design | Plate seat |
| Nominal width | 7 mm |
| Type of control | directly |
| Symbol | 00991700 |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Actuating force | 2 N |
| Product weight | 510 g |
| Type of mounting | With through-hole |
| Pneumatic connection 1 | G1/4 |
| Pneumatic connection 2 | G1/4 |
| Pneumatic connection 3 | G1/4 |
| Pneumatic connection 4 | G1/4 |
| Pneumatic connection 5 | G1/4 |
| Seals material | NBR |
| Housing material | Die-cast aluminum |