

# Plastic-coated metal tube PM-6

Part number: 9087

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Outside diameter	8 mm
Bending radius relevant for flow rate	25 mm
Inside diameter	5.2 mm
Temperature-dependent operating pressure	-0.95 bar ... 30 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-29 °C ... 65 °C
Product weight by length	0.032 kg/m
Color	Black
Note on materials	RoHS compliant
Material of pneumatic tubing	Wrought aluminum alloy Protective grounding