


Stem actuated valve VO-3-1/4-B

Part number: 9157

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Valve function	3/2-way, monostable, open
Actuation type	Mechanical
Normal nominal flow rate (normalized to DIN 1343)	600 l/min
Pneumatic working port	G1/4
Operating pressure	-0.95 bar ... 10 bar
Structural design	Plate seat
Nominal width	7 mm
Type of control	directly
Symbol	00991138
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Actuating force	128 N
Product weight	130 g
Type of mounting	With through-hole
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Pneumatic connection 3	G1/4
Seals material	NBR
Housing material	Die-cast aluminum