

Adapter AD-G1/8-1/8NPT-I

Part number: 9395

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal width	5.95 mm
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque, pneumatic connection 1	6 Nm
Max. tightening torque, pneumatic connection 2	7 Nm
Nominal tightening torque	10.55 Nm
Tolerance for nominal tightening torque	±20%
Product weight	10.38 g
Pneumatic connection 1	External thread G1/8
Pneumatic connection 2	Internal thread 1/8 NPT
Note on materials	RoHS compliant
Seals material	PVC
Housing material	Steel, galvanized