

Adapter AD-G1/2-1/2NPT-I

FESTO

Part number: 9398



 [General operating condition](#)

Data sheet

Feature	Value
Nominal width	14.3 mm
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque, pneumatic connection 1	40 Nm
Max. tightening torque, pneumatic connection 2	28 Nm
Nominal tightening torque	47.9 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	51.89 g
Pneumatic connection 1	External thread G1/2
Pneumatic connection 2	Female thread 1/2 NPT
Note on materials	RoHS-compliant
Seals material	PVC
Housing material	Steel, galvanized