


# Bulkhead quick connector SCK-PK-9

Part number: 9423

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal width	8 mm
Mounting position	Any
Design	Bulkhead
Operating pressure for entire temperature range	0 MPa ... 1.6 MPa
Operating pressure for entire temperature range	0 bar ... 16 bar
Operating pressure for entire temperature range	0 psi ... 232 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C ... 150 °C
Pneumatic connection 1	For barbed fitting, inside diameter 9 mm, with union nut
Pneumatic connection 2	for barbed fitting, inside diameter 9 mm, with nut
Material of union nut	Wrought aluminum alloy, anodized
Note on materials	RoHS-compliant
Nut material	Steel, galvanized
Connector material	Wrought aluminum alloy, anodized