

Flow control/muffler GRU-1/8-B

Part number: 9516

FESTO



 General operating condition

Data sheet

Feature	Value
Valve function	Sound pressure flow control function
Selection of additional function	with muffler
Pneumatic connection 1	G1/8
Adjusting element	Slotted screw
Type of mounting	Screw-in
Standard flow rate 6->0 bar	0 l/min ... 1000 l/min
Ambient temperature	-10 °C ... 70 °C
Housing material	Aluminum
Mounting position	Any
Symbol	00991451
Operating pressure for entire temperature range	0 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Temperature of medium	-10 °C ... 70 °C
Product weight	10 g
Cushioning insert material	Protective grounding
Material of screwed plug	Die-cast aluminum
Note on materials	RoHS compliant
Material of adjusting screw	PA