

Ball valve QH-1/4

Part number: 9541

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Valve function	2/2 bistable
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Actuation type	Manual
Type of mounting	Line installation
Normal nominal flow rate (normalized to DIN 1343)	3400 l/min
Nominal width	12 mm
Housing material	Brass
Sealing principle	Soft
Mounting position	Any
Conforms to standard	ISO 228-1
Structural design	Ball valve
Symbol	00991458
Nominal pressure of fitting PN	40
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Medium	Compressed air as per ISO 8573-1:2010 [-:~:] Inert gas Water – no water vapor Neutral liquids Other flow media on request
Temperature of medium	-20 °C ... 150 °C
Product weight	180 g
Seals material	FPM PTFE
Ball material	Brass, chrome-plated
Shaft material	Brass