

Adapter AD-1/8NPT-G1/8-I

Part number: 9624

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|--------------------------|
| Nominal width | 5.95 mm |
| Operating pressure for entire temperature range | -0.95 bar ... 10 bar |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Max. tightening torque, pneumatic connection 1 | 7 Nm |
| Max. tightening torque, pneumatic connection 2 | 6 Nm |
| Product weight | 9.5 g |
| Pneumatic connection 1 | external thread 1/8 NPT |
| Pneumatic connection 2 | Internal thread G1/8 |
| Note on materials | RoHS compliant |
| Seals material | PVC |
| Housing material | Steel, galvanized |