

Adapter AD-3/8NPT-G3/8-I

Part number: 9626

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Nominal width	11.5 mm
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque, pneumatic connection 1	22 Nm
Max. tightening torque, pneumatic connection 2	25 Nm
Product weight	25.98 g
Pneumatic connection 1	external thread 3/8 NPT
Pneumatic connection 2	Internal thread G3/8
Note on materials	RoHS compliant
Seals material	PVC
Housing material	Steel, galvanized