

Double nipple E-G1/4-1/4NPT

Part number: 9631

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|---|---|
| Nominal width | 7.95 mm |
| Operating pressure for entire temperature range | -0.95 bar ... 10 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Lubricated operation possible |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -10 °C ... 60 °C |
| Max. tightening torque, pneumatic connection 1 | 11 Nm |
| Max. tightening torque, pneumatic connection 2 | 12 Nm |
| Nominal tightening torque | 9.05 Nm |
| Tolerance for nominal tightening torque | ±20% |
| Product weight | 19.06 g |
| Pneumatic connection 1 | G1/4 |
| Pneumatic connection 2 | 1/4 NPT |
| Note on materials | RoHS compliant |