

# Double nipple E-G1/2-1/2NPT

Part number: 9633

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Nominal width	14.3 mm
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C ... 60 °C
Max. tightening torque, pneumatic connection 1	40 Nm
Max. tightening torque, pneumatic connection 2	28 Nm
Nominal tightening torque	47.9 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	47.68 g
Pneumatic connection 1	G1/2
Pneumatic connection 2	1/2 NPT
Note on materials	RoHS-compliant