

# Servo motor EMMT-AS-80-H-HS-RSB

Part number: 610908

FESTO



 [General operating condition](#)

## Datasheet product reliability

The information in this "Product reliability data sheet" is based on products being used as intended. This includes complying with all specifications in data sheets, catalogues, user documentation and the general operating conditions. The user alone is responsible for determining whether a product is suitable for a particular application.

| Feature                                                 | Value                                                                                           |
|---------------------------------------------------------|-------------------------------------------------------------------------------------------------|
| Certificate issuing authority                           | UL E342973                                                                                      |
| Mean time to failure (MTTF), subcomponent <sup>1)</sup> | 190 years, rotor position sensor                                                                |
| Switching cycles holding brake                          | 10 million idle actuations (without friction work!)                                             |
| Vibration resistance                                    | Transport application test with severity level 2 in accordance with FN942017-4 and EN 60068-2-6 |
| Shock resistance                                        | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27               |
| CE mark (see declaration of conformity)                 | To EU EMC Directive<br>To EU RoHS Directive<br>To EU Low Voltage Directive                      |

1) The ascertainment of the MTTF value is based on the IEC 61709 "Electric components - Reliability - Reference conditions for failure rates and stress models for conversion" respectively on the SN 29500.