




Solenoid valve VUVG-L10-T32C-MZT-M5-1H2L-F1A

Part number: 8164332

FESTO



 [General operating condition](#)

Datasheet product reliability

The information in this "Product reliability data sheet" is based on products being used as intended. This includes complying with all specifications in data sheets, catalogues, user documentation and the general operating conditions. The user alone is responsible for determining whether a product is suitable for a particular application.

| Feature | Value |
|---|---|
| Certificate issuing authority | UL MH19482 |
| Service-life value B_{10} ¹⁾ | 27 Mio cycles |
| Design characteristics | Mechanical spring return |
| Lap | Overlap |
| Vibration resistance | Transport application test with severity level 2 in accordance with FN942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27 |
| Max. positive test pulse with 0 signal | 700 μ s |
| Max. negative test pulse with 1 signal | 900 μ s |

1) The ascertainment of characteristic service life values is based on the ISO 19973 "Pneumatic fluid power - Assessment of component reliability by testing".