


Soldering base PCBC

**FESTO**



Datasheet

| General technical data |                     |
|------------------------|---------------------|
| Electrical connection  | 2-pin               |
| Type of mounting       | With soldering base |
| Mounting position      | Any                 |
| Degree of protection   | IP40                |
| Product weight         | 5 g                 |


| Materials        |    |
|------------------|----|
| Material housing | PA |

| Operating and environmental conditions |               |
|----------------------------------------|---------------|
| Ambient temperature                    | -40 ... 115°C |

Dimensions


Dimensions – Soldering base PCBC

Download CAD data [www.festo.com](http://www.festo.com)



|        | B1<br>±0,1 | B2<br>±0,15 | D1<br>Ø | H1 | L1   | L2   |
|--------|------------|-------------|---------|----|------|------|
| PCBC-A | 8          | 4           | 0,6     | 4  | 12,7 | 10,2 |

Ordering data

| PCBC                                                                             |                             |          |            |
|----------------------------------------------------------------------------------|-----------------------------|----------|------------|
|                                                                                  | Packaging quantity [pieces] | Part no. | Type       |
|  | 10                          | 197261   | PCBC-A-10  |
|                                                                                  | 100                         | 197262   | PCBC-A-100 |