Manifold rail
VABM-C8-12E-G14-35-PT-L

Part number: 1247987

General operating condition

Data sheet

Feature	Value
Grid dimension	12 mm
Max. number of valve positions	35
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Max. tightening torque for valve mounting	0.6 Nm
Max. tightening torque wall mounting	5 Nm
Product weight	2138 g
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 3	G1/4
Pneumatic connection, port 5	G1/4