

# Proximity sensor SIEN-6,5B-NO-S-L

Part number: 150381

FESTO



[General operating condition](#)

## Data sheet

| Feature  | Value  |
|--|--|
| Conforms to standard                                 | EN 60947-5-2   |
| Symbol   | 00991645   |
| Approval   | RCM<br>c UL us - Listed (Oil)  |
| CE mark (see declaration of conformity)              | To EU EMC Directive<br>In accordance with EU RoHS Directive  |
| UKCA marking (see declaration of conformity)         | according to UK RoHS instructions (UK-R)   |
| Rated operating distance                             | 1.5 mm   |
| Assured operating distance                           | 1.21 mm  |
| Reduction factors                                    | Aluminium = 0.25<br>Stainless steel St 18/8 = 0.7<br>Copper = 0.2<br>Brass = 0.35<br>Steel St 37 = 1.0 |
| Ambient temperature                                  | -25 °C ... 70 °C   |
| Repetition accuracy with constant conditions         | 0.07 mm  |
| Switching output                                     | NPN  |
| Switching element function                           | N/C contact  |
| Hysteresis   | ≤0.07 mm   |
| Max. switching frequency                             | 5000 Hz  |
| Max. output current                                  | 200 mA   |
| Voltage drop   | ≤2 V   |
| Inductive protective circuit                         | Integrated   |
| Short circuit current rating                         | Pulsed   |
| Operational voltage range DC                         | 10 V ... 30 V  |
| Residual ripple                                      | ± 10%  |
| No-load supply current                               | ≤10 mA   |
| Reverse polarity protection                          | For all electrical connections   |
| Electrical connection 1, connection type             | Plug   |
| Electrical connection 1, connector system            | M8x1, A-coded, to EN 61076-2-104   |
| Electrical connection 1, number of connections/cores | 3  |
| Electrical connection 1, type of mounting            | Not rotatable  |
| Electrical connection 1, compatible type of mounting | Compatible with latching lock<br>Compatible with rotatable screw-type lock                             |
| Size   | 6.5 mm   |
| Type of mounting                                     | Clamped  |
| Mounting type  | Flush  |
| Product weight                                       | 4 g  |

| <b>Feature</b>                              | <b>Value</b>                                |
|---|---|
| Material housing                            | High-alloy stainless steel<br>Chrome-plated |
| Switching status indication                 | Yellow LED                                  |
| Ambient temperature with moving cable       | -5 °C ... 70 °C                             |
| Degree of protection                        | IP65<br>IP67                                |
| Corrosion resistance class CRC              | 2 - Moderate corrosion stress               |
| LABS (PWIS) conformity                      | VDMA24364-B2-L                              |
| Additional information for sensor selection | With standards-based switching distance     |
| Electrical output                           | NPN   |
| Selection of sensor design                  | Standard                                    |