

Proximity sensor SIEN-M5B-PO-K-L

Part number: 150374

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Conforms to standard	EN 60947-5-2
Symbol	00991613
Approval	RCM c UL us - Listed (Oil)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	according to UK RoHS instructions (UK-R)
Note on materials	RoHS compliant
Rated operating distance	0.8 mm
Ambient temperature	-25 °C ... 70 °C
Repetition accuracy with constant conditions	0.01 mm
Switching output	PNP
Switching element function	N/C contact
Max. switching frequency	5000 Hz
Max. output current	200 mA
Short circuit current rating	Pulsed
Operational voltage range DC	10 V ... 30 V
Reverse polarity protection	For all electrical connections
Electrical connection 1, connection type	Cable
Electrical connection 1, connector system	Open end
Electrical connection 1, number of connections/cores	3
Cable length	2.5 m
Material cable sheath	TPE-U(PUR)
Size	M5x0.5
Type of mounting	Via lock nut
Tightening torque	1.5 Nm
Mounting type	Flush
Product weight	33.6 g
Material housing	High-alloy stainless steel
Switching status indication	Yellow LED
Ambient temperature with moving cable	-5 °C ... 70 °C
Degree of protection	IP67
Immunity to surge	1 kV
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Pollution degree	3

Feature	Value
Additional information for sensor selection	With standards-based switching distance
Electrical output	PNP
Selection of sensor design	Standard