

Proximity sensor SIEN-6,5B-PS-S-L

Part number: 150379

FESTO



[General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Conforms to standard | EN 60947-5-2 |
| Symbol | 00991701 |
| Approval | RCM c UL us - Listed (Oil) |
| CE mark (see declaration of conformity) | To EU EMC Directive In accordance with EU RoHS Directive |
| UKCA marking (see declaration of conformity) | according to UK RoHS instructions (UK-R) |
| Rated operating distance | 1.5 mm |
| Assured operating distance | 1.21 mm |
| Reduction factors | Aluminium = 0.25 Stainless steel St 18/8 = 0.7 Copper = 0.2 Brass = 0.35 Steel St 37 = 1.0 |
| Ambient temperature | -25 °C ... 70 °C |
| Repetition accuracy with constant conditions | 0.07 mm |
| Switching output | PNP |
| Switching element function | N/O contact |
| Hysteresis | ≤0.07 mm |
| Max. switching frequency | 5000 Hz |
| Max. output current | 200 mA |
| Voltage drop | ≤2 V |
| Inductive protective circuit | Integrated |
| Short circuit current rating | Pulsed |
| Operational voltage range DC | 10 V ... 30 V |
| Residual ripple | ± 10% |
| No-load supply current | ≤10 mA |
| Reverse polarity protection | For all electrical connections |
| Electrical connection 1, connection type | Plug |
| Electrical connection 1, connector system | M8x1, A-coded, to EN 61076-2-104 |
| Electrical connection 1, number of connections/cores | 3 |
| Electrical connection 1, type of mounting | Not rotatable |
| Electrical connection 1, compatible type of mounting | Compatible with latching lock Compatible with rotatable screw-type lock |
| Size | 6.5 mm |
| Type of mounting | Clamped |
| Mounting type | Flush |
| Product weight | 4 g |

| Feature | Value |
|---|---|
| Material housing | High-alloy stainless steel Chrome-plated |
| Switching status indication | Yellow LED |
| Ambient temperature with moving cable | -5 °C ... 70 °C |
| Degree of protection | IP65 IP67 |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Additional information for sensor selection | With standards-based switching distance |
| Electrical output | PNP |
| Selection of sensor design | Standard |