

Solenoid valve MN1H-2-1/2-MS

Part number: 161728

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Design	Diaphragm valve
Type of actuation	Electrical
Sealing principle	Soft
Mounting position	Any
Type of mounting	Inline installation
Connection Process valve	G1/2
Electrical connection	Plug To DIN EN 175301-803 Square design
Nominal size	13 mm
Valve function	2/2-way, single solenoid, closed
Manual override	Detenting via accessory Non-detenting
Flow direction	Non-reversible
Medium	Filtered compressed air, grade of filtration 200 µm
Exhaust-air function	Cannot be throttled
Characteristic coil data	230 V AC: 50 Hz, pick-up power 5.0 VA, holding power 3.7 VA 230 V AC: 60 Hz, pick-up power 5.0 VA, holding power 3.7 VA 24 V DC: 2.5 W
Type of reset	Pneumatic spring
Type of piloting	Piloted
Symbol	00991399
Medium pressure	0.5 bar ... 10 bar
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Media temperature	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Standard nominal flow rate (standardised to DIN 1343)	3100 l/min
Switching time on	30 ms
Switching time off	100 ms
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Material housing	Brass
Material screws	High-alloy stainless steel
Material number screw	1,4301
Product weight	400 g
Degree of protection	IP65 With plug socket