

Solenoid valve CPV18-M1H-5LS-1/4

Part number: 163190

FESTO



[PDF General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Valve function | 5/2-way, single solenoid |
| Type of actuation | Electrical |
| Valve size | 18 mm |
| Standard nominal flow rate (standardised to DIN 1343) | 1600 l/min |
| pneumatic working port | G1/4 |
| Operating voltage | 24 V DC |
| Operating pressure | -0.09 MPa ... 1 MPa |
| Operating pressure | -0.9 bar ... 10 bar |
| Design | Piston gate valve |
| Type of reset | Pneumatic spring |
| Approval | C-Tick |
| Degree of protection | IP65 |
| Nominal size | 8 mm |
| Exhaust-air function | Cannot be throttled |
| Sealing principle | Soft |
| Mounting position | Any |
| Manual override | Detenting Non-detenting |
| Type of piloting | Piloted |
| Pilot air supply | External Internal |
| Flow direction | Non-reversible |
| Symbol | 00991027 |
| lap | Overlap |
| Pilot pressure | 0.3 MPa ... 0.8 MPa |
| Pilot pressure | 3 bar ... 8 bar |
| b value | 0.38 |
| C value | 6.3 l/sbar |
| Switching time off | 26 ms |
| Switching time on | 18.5 ms |
| Duty cycle | 100% |
| Electrical power consumption | 1.5 W |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |

| Feature | Value |
|-----------------------------------|--|
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Storage temperature | -20 °C ... 40 °C |
| Media temperature | -5 °C ... 50 °C |
| Ambient temperature | -5 °C ... 50 °C |
| Product weight | 260 g |
| Type of mounting | With through-hole |
| Pilot air port 12/14 | Common line |
| Pilot exhaust port 82/84 | Common line |
| Pneumatic connection, port 1 | Common line |
| Pneumatic connection, port 11 | Common line |
| Pneumatic connection, port 2 | G1/4 |
| Pneumatic connection 3/5 combined | Common line |
| Pneumatic connection, port 4 | G1/4 |
| Note on materials | RoHS compliant |
| Material seals | HNBR NBR |
| Material housing | Die-cast aluminium Brass POM PPS Steel |