

Guided drive DFM-25-25-P-A-GF

Part number: 170848

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|--|--|
| Distance from centre of gravity of load to yoke plate xs | 50 mm |
| Stroke | 25 mm |
| Piston diameter | 25 mm |
| Operating mode, drive unit | Yoke |
| Cushioning | Elastic cushioning rings/plates at both ends |
| Mounting position | Any |
| Guide | Plain-bearing guide |
| Design | Guidance |
| Position detection | Via proximity switch |
| Symbol | 00991737 |
| Operating pressure | 0.15 MPa ... 1 MPa |
| Operating pressure | 1.5 bar ... 10 bar |
| Max. speed | 0.8 m/s |
| Mode of operation | Double-acting |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Cleanroom suitability, measured according to ISO 14644-14 | Class 6 according to ISO 14644-1 |
| Ambient temperature | -20 °C ... 80 °C |
| Impact energy in end positions | 0.3 J |
| Max. force Fy | 810.7 N |
| Max. force Fy static | 810.7 N |
| Max. force Fz | 810.7 N |
| Max. force Fz static | 810.7 N |
| Max. moment Mx | 27.56 Nm |
| Max. torque Mx static | 27.56 Nm |
| Max. moment My | 15.4 Nm |
| Max. torque My static | 15.4 Nm |
| Max. moment Mz | 15.4 Nm |
| Max. torque Mz static | 15.4 Nm |
| Max. permissible torque load Mx as a function of stroke | 5.9 Nm |
| Max. effective load dependent upon stroke at defined distance xs | 116 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke | 247 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 295 N |

| Feature | Value |
|-------------------------|----------------------------|
| Moving mass | 669 g |
| Product weight | 1308 g |
| alternative connections | See product drawing |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS compliant |
| Material cover | Wrought aluminium alloy |
| Material seals | NBR |
| Material housing | Wrought aluminium alloy |
| Material piston rod | High-alloy stainless steel |