


DUO cable NEDU-L1R2-V9-M12G8-E-LE5-5R1-LE3-5R2

Part number: 2903567



 General operating condition

Data sheet

Feature	Value
Based on standard	EN 61076-2-101
Design	Y-distributor with cable on field device and controller side
Distribution	1 to 2
Additional functions	Connection of sensor and controller to proportional pressure regulator
Cable designation	Without inscription label holder
Product weight	377 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 1, number of connections/cores	8
Electrical connection 1, used connections/cores	6
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection 1, connection pattern	00992265
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connector system	Open end
Electrical connection 2, number of connections/cores	5
Electrical connection 2, used connections/cores	5
Electrical connection 3, function	Field device side
Electrical connection 3, connection type	Cable
Electrical connection 3, connector system	Open end
Electrical connection 3, number of connections/cores	3
Electrical connection 3, used connections/cores	3
Operational voltage range DC	0 V ... 30 V
Operational voltage range AC	0 V ... 30 V
Current rating at 40° C	2 A
Immunity to surge	0.8 kV
Shielding	Yes
Cable length 1	5 m
Cable length 2	5 m
Cable diameter 1	5.3 mm
Cable diameter 2	4.5 mm
Cable structure	3 x 0.25 mm ² 5 x 0.25 mm ²

Feature	Value
Nominal cross section conductor	0.25 mm ²
Degree of protection	IP65 IP67
Note on degree of protection	In mounted state
Ambient temperature	-25 °C ... 80 °C
Ambient temperature with moving cable	-5 °C ... 80 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS compliant
Pollution degree	3
Corrosion resistance class CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Cable sheath colour	Black
Material housing	TPE-U(PUR)
Housing colour	Black
Material screw-type lock	Brass, nickel-plated
Material seals	Fluoro rubber
Material electrical contact	Gold-plated brass
Material insulating sheath	PVC