

Solenoid valve

JMFH-5/2-D-2-S-C-EX

Part number: 535967

FESTO



[PDF](#) General operating condition

Data sheet

| Feature | Value |
|---|---|
| Valve function | 5/2-way, double solenoid |
| Type of actuation | Electrical |
| Construction width | 54 mm |
| Standard nominal flow rate (standardised to DIN 1343) | 2300 l/min |
| pneumatic working port | Sub-base size 2 to ISO 5599-1 G3/8 |
| Operating voltage | Via solenoid coil, must be ordered separately |
| Operating pressure | -0.09 MPa ... 1.6 MPa |
| Operating pressure | -0.9 bar ... 16 bar |
| Design | Piston gate valve |
| CE mark (see declaration of conformity) | To EU Explosion Protection Directive (ATEX) |
| UKCA marking (see declaration of conformity) | To UK EX instructions |
| ATEX category gas | II 2G |
| ATEX category dust | II 2D |
| Explosion ignition protection type for gas | Ex h IIC T4 Gb |
| Explosion ignition protection type for dust | Ex h IIIC T105°C Db |
| Explosion ambient temperature | -5°C ≤ Ta ≤ +40°C |
| Explosion protection certification outside the EU | EPL Db (GB) EPL Gb (GB) |
| Degree of protection | IP65 |
| Nominal size | 11.5 mm |
| Grid dimension | 56 mm |
| Exhaust-air function | Can be throttled |
| Sealing principle | Soft |
| Mounting position | Any |
| Conforms to standard | ISO 5599-1 |
| Manual override | Detenting via accessory Non-detenting |
| ISO code | 269 |
| Type of piloting | Piloted |
| Pilot air supply | External |
| Flow direction | Reversible |
| Symbol | 00991067 |
| lap | Overlap |
| Pilot pressure | 0.2 MPa ... 1 MPa |
| Pilot pressure | 2 bar ... 10 bar |

| Feature | Value |
|--|---|
| Suitability for vacuum | Yes |
| Switching time reversal | 18 ms |
| Max. positive test pulse with 0 signal | 2200 µs |
| Max. negative test pulse with 1 signal | 3700 µs |
| Explosion protection | Zone 1 (ATEX) Zone 1 (UKEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 21 (UKEX) Zone 22 (ATEX) |
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Vibration resistance | Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6 |
| Shock resistance | Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27 |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Media temperature | -10 °C ... 60 °C |
| Sound pressure level | 85 dB(A) |
| Pilot medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Ambient temperature | -5 °C ... 40 °C |
| Product weight | 820 g |
| Electrical connection | Via F coil, to be ordered separately |
| Type of mounting | On sub-base Via through-hole and screw |
| Pilot exhaust port 82 | M5 |
| Pilot exhaust port 84 | M5 |
| Pilot air port 12 | Sub-base size 2 to ISO 5599-1 |
| Pilot air port 14 | Sub-base size 2 to ISO 5599-1 |
| Pneumatic connection, port 1 | Sub-base size 2 to ISO 5599-1 |
| Pneumatic connection, port 2 | Sub-base size 2 to ISO 5599-1 |
| Pneumatic connection, port 3 | Sub-base size 2 to ISO 5599-1 |
| Pneumatic connection, port 4 | Sub-base size 2 to ISO 5599-1 |
| Pneumatic connection, port 5 | Sub-base size 2 to ISO 5599-1 |
| Note on materials | RoHS compliant |
| Material seals | HNBR NBR |
| Material housing | Die-cast aluminium |