

# Solenoid valve MFH-5-1/4-L-B

Part number: 31010

FESTO



General operating condition

## Data sheet

| Feature   | Value  |
|---|--|
| Valve function  | 5/2-way, single solenoid   |
| Type of actuation                                     | Electrical   |
| Construction width                                    | 32 mm  |
| Standard nominal flow rate (standardised to DIN 1343) | 1600 l/min   |
| pneumatic working port                                | G1/4   |
| Operating pressure                                    | 0.3 MPa ... 1 MPa  |
| Operating pressure                                    | 3 bar ... 10 bar   |
| Design  | Piston gate valve  |
| Type of reset   | Pneumatic spring   |
| Nominal size  | 10 mm  |
| Grid dimension  | 33 mm  |
| Exhaust-air function                                  | Can be throttled   |
| Sealing principle                                     | Soft   |
| Mounting position                                     | Any  |
| Manual override                                       | Non-detenting  |
| Type of piloting                                      | Piloted  |
| Pilot air supply                                      | Internal   |
| Flow direction  | Non-reversible   |
| Symbol  | 00991023   |
| lap   | Overlap  |
| b value   | 0.38   |
| C value   | 6.35 l/sbar  |
| Max. switching frequency                              | 3 Hz   |
| Switching time off                                    | 42 ms  |
| Switching time on                                     | 23 ms  |
| Max. positive test pulse with 0 signal                | 2200 µs  |
| Max. negative test pulse with 1 signal                | 3700 µs  |
| Operating medium                                      | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium                    | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                        | 1 - Low corrosion stress   |
| LABS (PWIS) conformity                                | VDMA24364-B1/B2-L  |
| Storage temperature                                   | -40 °C ... 60 °C   |
| Media temperature                                     | -10 °C ... 60 °C   |
| Ambient temperature                                   | -5 °C ... 40 °C  |
| Product weight  | 380 g  |

| <b>Feature</b>               | <b>Value</b>                         |
|------------------------------|--------------------------------------|
| Electrical connection        | Via F coil, to be ordered separately |
| Type of mounting             | On PR rail<br>With through-hole      |
| Pilot exhaust port 84        | M5                                   |
| Pneumatic connection, port 1 | G1/4                                 |
| Pneumatic connection, port 2 | G1/4                                 |
| Pneumatic connection, port 3 | G1/4                                 |
| Pneumatic connection, port 4 | G1/4                                 |
| Pneumatic connection, port 5 | G1/4                                 |
| Note on materials            | RoHS compliant                       |
| Material seals               | NBR                                  |
| Material housing             | Die-cast aluminium                   |