

Ball valve VAPB-1 1/2-F-25-F0405

Part number: 534308

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Design	2-way ball valve
Type of actuation	Mechanical
Sealing principle	Soft
Mounting position	optional
Type of mounting	In-line installation
Connection Process valve	Rp1 1/2
Switching position indicator	Slot direction = flow direction
Flange hole pattern	F04 F05
Inside diameter	40 mm
Nominal size DN	40
Valve function	2/2
Flow direction	Reversible
Nominal pressure PN	25
Breakaway torque at differential pressure, nominal pressure, process valve PN	19 Nm
Break-away torque at a differential pressure of 1 MPa (10 bar, 145 psi)	14.9 Nm
Based on standard	ISO 5211
Symbol	00991458
Medium	Compressed air to ISO 8573-1:2010 [-:~:] Inert gases Water Neutral fluids
Media temperature	-20 °C ... 150 °C
Flow rate Kv	200 m ³ /h
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Material housing	Brass, nickel-plated
Material number housing	2.0402 CW617N

Feature	Value
Material seat seal	PTFE
Material seals	HNBR PTFE
Material ball	Brass Hard-chrome-plated
Material number ball	2.0402 CW617N
Material shaft	Brass
Material number shaft	2.0401 CW614N
Product weight	1900 g
Corrosion resistance class CRC	1 - Low corrosion stress