

Fine filter MS4-LFM-1/4-BRM-DA

Part number: 536818

FESTO



[PDF General operating condition](#)

Data sheet

| Feature | Value |
|---|--|
| Series | MS |
| Size | 4 |
| Design | Fibre filter |
| Grade of filtration | 1 µm |
| Condensate drain | Manual, rotating |
| Symbol | 00991543 |
| Operating pressure | 0 MPa ... 1.4 MPa |
| Operating pressure | 0 bar ... 14 bar |
| Operating pressure | 0 psi ... 203 psi |
| Operating medium | Compressed air to ISO 8573-1:2010 [6:-:4] Inert gas |
| Air purity class at output | Compressed air to ISO 8573-1:2010:[5:-:3] |
| Max. standard flow rate for clean air class | 360 l/min |
| Min. standard flow rate for clean air class | 54 l/min |
| Filter efficiency | 99.99 % |
| Max. condensate volume | 19 ml |
| Bowl guard | Plastic bowl guard |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Suitable for use with food | See supplementary material information |
| Media temperature | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Storage temperature | -10 °C ... 60 °C |
| Filter efficiency, fine particles | 99 % |
| Residual oil content | 0.5 mg/m ³ |
| Filter efficiency, oil aerosol | 90 % |
| Differential pressure display | Visual indicator |
| Type of mounting | With accessories |
| Mounting position | Vertical +/-5° |
| Pneumatic connection, port 1 | G1/4 |
| Pneumatic connection, port 2 | G1/4 |
| Material housing | Die-cast aluminium |

| Feature | Value |
|-------------------|--------------------|
| Material filter | Borosilicate fibre |
| Material bowl | Makrolon® |
| Material seals | NBR |
| Note on materials | RoHS compliant |
| Product weight | 190 g |