

# Proximity sensor SME-8M-ZS-24V-K-2,5-OE

Part number: 543872

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Symbol	00991624
Approval	RCM c UL us - Listed (Oil)
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
Special characteristics	Oil-resistant
Note on materials	RoHS compliant
Instructions on use	<a href="https://www.festo.com/Drive-Sensor-Overview">https://www.festo.com/Drive-Sensor-Overview</a>
Measuring principle	Magnetic reed
Ambient temperature	-40 °C ... 70 °C
Switching output	Contacting, bipolar
Switching element function	N/O contact
Max. output current	80 mA
Max. output current using mounting kits	80 mA
Max. switching capacity AC	2.4 VA
Max. switching capacity DC	2.4 W
Max. switching capacity DC using mounting kits	2.4 W
Max. switching capacity AC using mounting kits	2.4 VA
Voltage drop	4.8 V
Short circuit current rating	No
Overload protection	Not provided
Operational voltage range AC	5 V ... 30 V
Operational voltage range DC	5 V ... 30 V
Reverse polarity protection	No
Electrical connection 1, connection type	Cable
Electrical connection 1, connector system	Open end
Electrical connection 1, number of connections/cores	2
Connection outlet orientation	In-line
Test conditions cable	Bending strength: to Festo standard Test conditions on request Energy chain: > 5 million cycles, bending radius 75 mm
Cable length	2.5 m
Cable characteristic	Standard/suitable for energy chains
Material cable sheath	TPE-U(PUR)
Type of mounting	Screw-clamped Insertable in the slot from above

<b>Feature</b>	<b>Value</b>
Product weight	26.3 g
Material housing	High-alloy stainless steel
Switching status indication	Yellow LED
Ambient temperature with moving cable	-5 °C ... 70 °C
Degree of protection	IP65 IP68
LABS (PWIS) conformity	VDMA24364-B2-L