

# Mini slide DGSL-25-200-PA

Part number: 544038

FESTO



 [General operating condition](#)

## Data sheet

| Feature  | Value  |
|--|--|
| Stroke   | 200 mm   |
| Adjustable end position range/length front                   | 110 mm   |
| Adjustable end position range/length rear                    | 49 mm  |
| Piston diameter  | 32 mm  |
| Operating mode, drive unit                                   | Yoke   |
| Cushioning   | Elastic cushioning rings/plates at both ends   |
| Mounting position  | Any  |
| Guide  | Ball bearing cage guide  |
| Design   | Yoke<br>Piston<br>Piston rod<br>Slide  |
| Position detection   | Via proximity switch   |
| Symbol   | 00991263   |
| Operating pressure   | 0.1 MPa ... 0.8 MPa  |
| Operating pressure   | 1 bar ... 8 bar  |
| Max. speed   | 0.8 m/s  |
| Repetition accuracy  | 0.3 mm   |
| Mode of operation  | Double-acting  |
| Operating medium   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 0 - No corrosion stress  |
| LABS (PWIS) conformity                                       | VDMA24364-B1/B2-L  |
| Cleanroom suitability, measured according to ISO 14644-14    | Class 7 according to ISO 14644-1   |
| Ambient temperature  | 0 °C ... 60 °C   |
| Impact energy in end positions                               | 0.55 J   |
| Cushioning length  | 1.3 mm   |
| Max. force F <sub>y</sub>                                    | 4800 N   |
| Max. force F <sub>z</sub>                                    | 4800 N   |
| Max. moment M <sub>x</sub>                                   | 130 Nm   |
| Max. moment M <sub>y</sub>                                   | 80 Nm  |
| Max. moment M <sub>z</sub>                                   | 80 Nm  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke  | 415 N  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 483 N  |
| Moving mass  | 2432 g   |
| Product weight   | 6351 g   |

| <b>Feature</b>          | <b>Value</b>               |
|-------------------------|----------------------------|
| alternative connections | See product drawing        |
| Type of mounting        | With through-hole          |
| Pneumatic connection    | G1/8                       |
| Note on materials       | RoHS compliant             |
| Material cover          | Wrought aluminium alloy    |
| Material seals          | HNBR                       |
| Material housing        | Wrought aluminium alloy    |
| Material piston rod     | High-alloy stainless steel |