

# Pneumatic valve VSPA-B-B52-A1

Part number: 546714

FESTO



[PDF](#) General operating condition

## Data sheet

| Feature   | Value  |
|---|--|
| Valve function  | 5/2-way, double solenoid   |
| Type of actuation                                     | Pneumatic  |
| Construction width                                    | 26 mm  |
| Standard nominal flow rate (standardised to DIN 1343) | 1100 l/min   |
| pneumatic working port                                | Sub-base size 26 mm to ISO 15407-1<br>Sub-base size 01 to VDMA 24563<br>G1/4               |
| Operating pressure                                    | -0.9 bar ... 16 bar  |
| Design  | Piston gate valve  |
| Nominal size  | 9 mm   |
| Exhaust-air function                                  | Can be throttled   |
| Sealing principle                                     | Soft   |
| Mounting position                                     | Any  |
| Conforms to standard                                  | ISO 15407-1<br>VDMA 24563  |
| Type of piloting                                      | Direct   |
| Flow direction  | Reversible   |
| Symbol  | 00991037   |
| lap   | Overlap  |
| Pilot pressure  | 2 bar ... 10 bar   |
| Flow rate of valve                                    | 1400 l/min   |
| Flow rate of valve on individual sub-base             | 1100 l/min   |
| Flow rate of pneumatically interlinked valve          | 1100 l/min   |
| Switching time reversal                               | 10 ms  |
| Explosion protection                                  | Zone 2 (ATEX)<br>Zone 22 (ATEX)  |
| Operating medium                                      | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on operating and pilot medium                    | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                        | 0 - No corrosion stress  |
| LABS (PWIS) conformity                                | VDMA24364-B1/B2-L  |
| Media temperature                                     | -10 °C ... 60 °C   |
| Relative air humidity                                 | 0 - 90%  |
| Pilot medium  | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Ambient temperature                                   | -10 °C ... 60 °C   |
| Max. tightening torque for valve mounting             | 1.8 Nm ... 2.2 Nm  |
| Product weight  | 180 g  |

| <b>Feature</b>               | <b>Value</b>                       |
|------------------------------|------------------------------------|
| Pilot air port 12            | Sub-base size 26 mm to ISO 15407-1 |
| Pilot air port 14            | Sub-base size 26 mm to ISO 15407-1 |
| Pneumatic connection, port 1 | Sub-base size 26 mm to ISO 15407-1 |
| Pneumatic connection, port 2 | Sub-base size 26 mm to ISO 15407-1 |
| Pneumatic connection, port 3 | Sub-base size 26 mm to ISO 15407-1 |
| Pneumatic connection, port 4 | Sub-base size 26 mm to ISO 15407-1 |
| Pneumatic connection, port 5 | Sub-base size 26 mm to ISO 15407-1 |
| Note on materials            | RoHS compliant                     |
| Material seals               | NBR                                |
| Material housing             | Die-cast aluminium                 |
| Material screws              | Steel<br>Galvanised                |