

Round cylinder DSNU-32-200-PPS-A

Part number: 559302

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Stroke	200 mm
Piston diameter	32 mm
Piston rod thread	M10x1.25
Cushioning	Self-adjusting pneumatic end-position cushioning
Mounting position	Any
Design	Piston Piston rod Cylinder barrel
Position detection	Via proximity switch
Symbol	00992970
Operating pressure	0.1 MPa ... 1 MPa
Operating pressure	1 bar ... 10 bar
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom suitability, measured according to ISO 14644-14	Class 6 according to ISO 14644-1
Ambient temperature	-20 °C ... 80 °C
Impact energy in end positions	0.4 J
Cushioning length	14 mm
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	415 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	482.5 N
Moving mass	301 g
Product weight	680 g
Type of mounting	With accessories
Pneumatic connection	G1/8
Note on materials	RoHS compliant
Material cover	Wrought aluminium alloy
Material seals	NBR TPE-U(PU)
Material piston rod	High-alloy steel
Material cylinder barrel	High-alloy stainless steel