

# Mini slide DGSL-8-20-EA

Part number: 570167

FESTO



[PDF](#) General operating condition

## Data sheet

| Feature                                                      | Value                                                                                      |
|--------------------------------------------------------------|--------------------------------------------------------------------------------------------|
| Stroke                                                       | 20 mm                                                                                      |
| Adjustable end position range/length front                   | 14.5 mm                                                                                    |
| Adjustable end position range/length rear                    | 3.5 mm                                                                                     |
| Piston diameter                                              | 10 mm                                                                                      |
| Operating mode, drive unit                                   | Yoke                                                                                       |
| Cushioning                                                   | Short elastic cushioning rings/pads at both ends                                           |
| Mounting position                                            | Any                                                                                        |
| Guide                                                        | Ball bearing cage guide                                                                    |
| Design                                                       | Yoke<br>Piston<br>Piston rod<br>Slide                                                      |
| Position detection                                           | Via proximity switch                                                                       |
| Symbol                                                       | 00991263                                                                                   |
| Operating pressure                                           | 0.15 MPa ... 0.8 MPa                                                                       |
| Operating pressure                                           | 1.5 bar ... 8 bar                                                                          |
| Max. speed                                                   | 0.8 m/s                                                                                    |
| Repetition accuracy                                          | 0.3 mm                                                                                     |
| Mode of operation                                            | Double-acting                                                                              |
| Operating medium                                             | Compressed air to ISO 8573-1:2010 [7:4:4]                                                  |
| Note on operating and pilot medium                           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                               | 0 - No corrosion stress                                                                    |
| LABS (PWIS) conformity                                       | VDMA24364-B1/B2-L                                                                          |
| Cleanroom suitability, measured according to ISO 14644-14    | Class 7 according to ISO 14644-1                                                           |
| Ambient temperature                                          | 0 °C ... 60 °C                                                                             |
| Impact energy in end positions                               | 0.08 J                                                                                     |
| Cushioning length                                            | 1.5 mm                                                                                     |
| Max. force F <sub>y</sub>                                    | 745 N                                                                                      |
| Max. force F <sub>z</sub>                                    | 745 N                                                                                      |
| Max. moment M <sub>x</sub>                                   | 8 Nm                                                                                       |
| Max. moment M <sub>y</sub>                                   | 5.5 Nm                                                                                     |
| Max. moment M <sub>z</sub>                                   | 5.5 Nm                                                                                     |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke  | 40 N                                                                                       |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke | 47 N                                                                                       |
| Moving mass                                                  | 111 g                                                                                      |
| Product weight                                               | 269 g                                                                                      |

| <b>Feature</b>          | <b>Value</b>               |
|-------------------------|----------------------------|
| alternative connections | See product drawing        |
| Type of mounting        | With through-hole          |
| Pneumatic connection    | M3                         |
| Note on materials       | RoHS compliant             |
| Material cover          | Wrought aluminium alloy    |
| Material seals          | HNBR                       |
| Material housing        | Wrought aluminium alloy    |
| Material piston rod     | High-alloy stainless steel |