

Programming cable VAVE-P8-VPS

Part number: 570971

FESTO



 General operating condition

Data sheet

Feature	Value
Conforms to standard	DIN 47100 EN 61076-2-101
Design	T-distributor with cable on controller side
Distribution	1 to 2
Additional functions	Programming interface for proportional pressure regulator
Cable designation	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 1, number of connections/cores	8
Electrical connection 1, used connections/cores	8
Electrical connection 1, type of mounting	Screw-type lock, size 14 mm
Electrical connection 1, connection pattern	00992265
Electrical connection 2, function	Control side
Electrical connection 2, design	Round
Electrical connection 2, connection type	Plug
Electrical connection 2, cable outlet	Straight
Electrical connection 2, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 2, number of connections/cores	8
Electrical connection 2, used connections/cores	8
Electrical connection 2, type of mounting	Screw-type lock, size 14 mm
Electrical connection 2, connection pattern	00992264
Electrical connection 3, function	Control side
Electrical connection 3, design	Round
Electrical connection 3, connection type	Socket
Electrical connection 3, cable outlet	Straight
Electrical connection 3, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 3, number of connections/cores	5
Electrical connection 3, used connections/cores	4
Electrical connection 3, type of mounting	Screw-type lock
Electrical connection 3, connection pattern	00991861
Operational voltage range DC	0 V ... 30 V
Operational voltage range AC	0 V ... 30 V
Current rating at 40° C	2 A

Feature	Value
Shielding	Yes
Cable length 1	0.15 m
Cable characteristic	Standard
Cable diameter 1	6.3 mm
Tolerance for cable diameter 1	±0.2 mm
Cable structure	8 x 0.25 mm ²
Nominal cross section conductor	0.25 mm ²
Degree of protection	IP65 IP67
Note on degree of protection	In mounted state
Ambient temperature	-25 °C ... 80 °C
Ambient temperature with moving cable	-5 °C ... 80 °C
CE mark (see declaration of conformity)	To EU EMC Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS compliant Free of halogen
Pollution degree	3
Corrosion resistance class CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Cable sheath colour	Grey
Material housing	TPE-U(PUR)
Housing colour	Black
Material screw-type lock	Nickel-plated die-cast zinc
Material seals	NBR
Material electrical contact	Gold-plated brass